

Installation Guide



l	Technical Data:								
	Column Stage	2 stage							
	Max Loading Capacity	80 KG / 176.4 LBS							
	Height Range	725 - 825 mm / 28.5 - 32.5 in							

Accessory List

Attention: The drawings below are for reference only, which might be slightly different from the actual product. Any missing tools or installation issues, please contact customer service.

No.	Image	Spec	Qty
А		M6×16mm	16
В	0	M6 washer	16
С	0	M8×16mm	8
D	0	M8 washer	8
E	©	M6×16mm	8
F		Allen Key 5x5mm	1
G		Allen Key 4x4mm	1
Н	Ø	ST4.8*16	16
I	0	M5 washer	16

2

(9)-

-10

5

(8)

(4)







Customer required

No.		Part						G	Qty I	No.			Part			Qty
6	<		\leq			T	able Board		1 (7	<			Tabl	e mat	1
No.	Part	Qty	No.	Part	Qty	No.	Part	Qty	No.	Part	Qty	No.	Part	Qty		
8	Headphone holder	1	9	Table board connector	4	10	Desktop piercing cover	3	(11)	A	8	(12)	Protective Sheet	1		



info@nitro-concepts.com www.nitro-concepts.com



Before turning over the desk, please adjust the height of the desk to your needs. Loosen the screws with the Allen key (G) and then pull on the pedestal, raising it to the height needed. To ensure the table legs are of the same length, please use



Caution

This product contains small items that can constitute a choking hazard if swallowed. Keep these items away from young children.

• This appliance can be used by children aged from 8 and up as well as people with reduced physical or sensory capacities with adequate instruction

· Please ensure the environment is safe prior to use e.g. do not leave tools unattended. Always dispose of unwanted plastic or packaging materials

